

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099000	-	LAM ASSY. SAME AS A552A021-01 SKN-2400	
C200099001	-	LAM SAME AS A552A020-101 SKN-2400	
C200099002	-	LAM ASSY SAME AS A552A026-01 SKN-2400	
C200099003	-	LAM SAME AS A552A027 SKN-2400	
C200099004	-	LAM ASSY SAME AS A552A023-01 SKN-2400	
C200099005	-	LAM SAME AS A552AA022-101 SKN-2400	
C200099006	-	TORQUE ASSY SAME AS K100A013-01 SKN-2400	
C200099007	-	INSULATION SLEEVING SAME AS Y110A005-040 SKN-2400	
C200099008	-	LAMINATION SAME AS A552A025-101	
C200099009	-	SPACER BLOCK SAME AS A308A184-101	
C200099010	-	MAGNET SAME AS A557A042-101	
C200099011	-	MAGNET KEEPER SAME AS A557A040-101	
C200099012	-	SODIUM DICHROMATE TECHNICAL GRADE TRIDENT	
C200099013	-	FREON TF REAGENT GRADE TRIDENT	
C200099014	-	METHYL ETHYL KEYTONE REAGENT GRADE TRIDENT	
C200099015	-	ACETONE REAGENT GRADE TRIDENT	
C200099016	-	TRICHLOROETHANE VG REAGENT GRADE(REF.101240029)	
C200099017	-	ISOPROPYL ALCOHOL REAGENT GRADE TRIDENT	
C200099018	-	SUPPORT-A333A865-101 FOR A201A412-01 TORQUER CUP	
C200099019	-	SPACER SAME AS 9208-PH115(A308A258-101)RN1W675	
C200099020	-	GLASS PREFORM B200051327-1 SKN-2400	
C200099021	-	PIN-B319001062-1 SKN-2400	
C200099022	-	PIN-A319A056-101 SKN-2400	
C200099023	-	Y113A005-101 MAG WIRE SPECIAL FOR B200071015 RN 15922-3	
C200099024	-	OIL-ES-OIL AMERICAN DURA FILM CO.INC.	
C200099025	-	MS122 FLOUROCARBON RELEASE AGENT DRY LUBE	
C200099026	-	Y108A012-101-MOLD MAT'L.FOR A201A412-01 TORQUER CUP	
C200099027	-	1/4" WD.WHT.POLYHEN KENDALL TAPE#765	
C200099028	-	1/2"WD.WHT.POLYHEN KENDALL TAPE#765	
C200099029	-	3/16"WD.WHT.POLYHEN KENDALL TAPE#765	
C200099030	-	STA.HSG.SAME AS C550031553-SOA#A896-DEI-02795	
C200099031	-	OBSOLETE-SUPERSEDED BY C200086524	
C200099032	-	OBSOLETE-SUPERSEDED BY C200086525	
C200099033	-	SAME AS SHIPPING FIXTURE 11-A200A765 T006	
C200099034	-	SAME AS PROTECTIVE MASK A333A143-101 T77	
C200099035	-	D C SILICONE RUBBER- S6538	
C200099036	-	PIN WIRE.015/.017 DIA. PER C190000211 TYPE 2	
C200099037	-	GEAR BLANK FOR C310082604 NOC#25438	
C200099038	-	FLEXIBLE PRINTED CABLE ASSY SAME AS A544A688-01	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099039	-	UNINSULATED ELEC.WIRE SAME AS Y112A001-126	
C200099040	-	ARMATURE TORQUE ASSY SAME AS A200A763-01	
C200099041	-	SPACER MAGNET SAME AS A308A182-101	
C200099042	-	MAGNET SAME AS A557A038-01	
C200099043	-	MAGNET RETAINER SAME AS A343A118-101	
C200099044	-	BRG.RETAINER SAME AS B318001157-1	
C200099045	-	BRG.RETAINER SAME AS B318001156-1	
C200099046	-	SHIM SAME AS B313001957-1	
C200099047	-	SHIM SAME AS B313001958-1	
C200099048	-	SHIM SAME AS B313001959-1	
C200099049	-	SHIM SAME AS B313001960-1	
C200099050	-	SHIM SAME AS B313001961-1	
C200099051	-	SHIM SAME AS B313001962-1	
C200099052	-	SHIM SAME AS B313001963-1	
C200099053	-	SHIM SAME AS B313001964-1	
C200099054	-	SHIM SAME AS B3130019651	
C200099055	-	SHIM SAME AS B313001966-1	
C200099056	-	ARMATURE &HSG ASSY SAME AS A508011-01	
C200099057	-	MAGNET & RETURN PATH SAME AS A557A043-01	
C200099058	-	SUPPORT BRUSH SAME AS A333A457-101	
C200099059	-	BRUSH & HOLDER SAME AS A558A034-101	
C200099060	-	MAGNET ASSY SAME AS A557A041-01	
C200099061	-	ARMATURE TORQUER SAME AS A200A766-01	
C200099062	-	TORQUER SUPORT PLATE SAME AS A300A464-101	
C200099063	-	SUPPORT BRUSH SAME AS A333A463-101	
C200099064	-	SCREW SAME AS A320A013-111	
C200099065	-	COIL FORM-SAME AS B506001040-1	
C200099066	-	T T TAGS(DRC FOR BENDIX UNITS)	
C200099067	-	INSULATOR-SAME AS B511001437-1	
C200099068	-	RETURN PATH-SAME AS A557A039-101	
C200099069	-	RETURN PATH SAME AS A557A036-101	
C200099070	-	COMMUTATOR SAME AS A555A003-101	
C200099071	-	HSG.SAME AS A314A151-101	
C200099072	-	LAMINATION-SAME AS B552001051-1	
C200099073	-	LAMINATION ASSY-SAME AS B552051049	
C200099074	-	COIL PICK-OFF SAME AS B200071010-1	
C200099075	-	BRUSH & HOLDER ASSY SAME AS A558A035-101	
C200099076	-	COIL FORM SAME AS B506001040-1	
C200099077	-	COMMUTATOR-SAME AS A555A004-101	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099078	-	HSG SAME AS A314A154-101	
C200099079	-	MOTOR ROTOR ASSY SAME AS A551A005-01	
C200099080	-	SUPPORT-SAME AS B333001560-1	
C200099081	-	LAMINATION-SAME AS A552A031-101	
C200099082	-	DATA IDENT.-SAME AS C360165422 EXCEPT PART NO TO BE CM41034124	
C200099083	-	RETURN PATH-SAME AS A557A054-101	
C200099084	-	STATOR BRACKET SAME AS A330A311-101	
C200099085	-	COMMUTATOR-SAME AS A555A005-101	
C200099086	-	BRUSH & HOLDER ASSY -SAME AS A558A040-101	
C200099087	-	RET PATH MAGNET-SAME AS A557A035-101	
C200099088	-	MAGNET-SAME AS A557A037-101	
C200099089	-	SAME AS C552052378 EXCEPT STACK HEIGHT .342 +.018 -.000	
C200099090	-	CONNECTOR-SAME AS LOCKHEED PART NO.LS10215R10-5PN AND LS12685R10A (BACKSHELL)	
C200099091	-	CLAMP,CAPACITOR-FOR ECONOLINE STEPPER	
C200099092	-	CAPACITOR-SAME AS CRS13D335KM (LINEAR BRUSHLESS)	
C200099093	-	GEAR BLANK-SAME AS C310102084 EXCEPT .3886 O.D	
C200099094	-	GEAR BLANK-SAME AS C310102085 EXCEPT .3954 O.D	
C200099095	-	GEAR BLANK-SAME AS C310102085 EXCEPT .4030 O.D	
C200099096	-	GEAR BLANK-SAME AS C310102086 EXCEPT .4030 O.D	
C200099097	-	GEAR BLANK-SAME AS C310102087 EXCEPT .3978 O.D.	
C200099098	-	SLOT WEDGE .010 X .040 X .540 MYLAR FOR A200A766-01	
C200099099	-	.080+ OR -.005 WIDE B101091014 TAPE SEE R.N#110779 (K100A013-01)	
C200099100	-	CERRO LOW ALLOY #147 (K100A013-01)	
C200099101	-	SAME AS A300A619-101 TORQ.SUPPORT PLATE (K100A015-02)	
C200099102	-	SAME AS A558A050-01 BRUSH & SUPPT.ASSY (K100A015-02)	
C200099103	-	SAME AS A308A226-101 LOCATING BUSHING (K100A015-02)	
C200099104	-	SCREW-SAME AS A320A298-101 (K100A015-02)	
C200099105	-	SAME AS A201A106-01 PT'D CABLE & SUPPORT	
C200099106	-		
C200099107	-		
C200099108	-		
C200099109	-	ROTOR FOR "Q" FORM UNIT CR40809048	
C200099110	-	STATOR SUPPORT-SAME AS A333A609-101	
C200099111	-	HEATER SAME AS A515A014-103	
C200099112	-	DATA IDENT.-SAME AS C360165410 EXCEPT PART NO TO BE CM41004083	
C200099113	-	491234310 WITH LUBE WASHED OUT	
C200099114	-	491244300 WITH LUBE WASHED OUT	
C200099115	-	491194310 WITH LUBE REMOVED	
C200099116	-	490274257-ID 080-82-79473 (SPARE PARTS)	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099117	-	BRUSH BLOCK-SAME AS 558042604 EXCEPT MADE ONLY IN ASHE.& CLEANED SPECIAL (SEE P. DILLINGHAM)	
C200099118	-	BRUSH BLOCK-SAME AS 558042600 EXCEPT MADE ONLY IN ASHE.& CLEANED SPECIAL (SEE P. DILLINGHAM)	
C200099119	-	HEAT SHRINK SLEEVING T.I.P/N 417177-9 (M41084026-M41034107)	
C200099120	-	EPOXY-RAYCHEMS-1009 T.I.P/N 417212-1(M41084026-M41034107)	
C200099121	-	DC-3144-CLEAR SILICON SEALER T.I P/N 417486-4 (M41084026-M41034107)	
C200099122	-	MAGNET-SAME AS A557A067-101	
C200099123	-	MAGNET SPACER-SAME AS A308A182-102	
C200099124	-	ROTOR SAME AS 551012263 EXCEPT EMI-50052 DATA	
C200099125	-	ROTOR SAME AS 551012263 EXCEPT EMI-50052 DATA	
C200099126	-	ROTOR SAME AS 551012263 EXCEPT EMI-50052 DATA	
C200099127	-	TORQUER-SAME AS A201A412-01	
C200099128	-	SAME AS A515A012-103 HEATER(FOR C550052526 STA & SUPPORT)	
C200099129	-	SAME AS 237-268 ROTOR EXCEPT CASTING REF. SOA#752	
C200099130	-	HELI-COIL	
C200099131	-	STA&SUPPT.-SAME AS 550052131 EXCEPT 200052074 MAG.WIRE & 750 TURNS	
C200099132	-	ROTOR-SAME AS 551071581 EXCEPT EMI-50052 DATA	
C200099133	-	ROTOR-SAME AS 551071581 EXCEPT EMI-50052 DATA	
C200099134	-	GEAR BLANK FOR C310132124	
C200099135	-	GEAR BLANK FOR C310132125	
C200099136	-	SAME AS 553002101 EXCEPT HAS NOTCH	
C200099137	-	MAG.SPACER-SAME AS A308A182-02	
C200099138	-	(SEE 200099071)	
C200099139	-	TORQUER-SAME AS A201A412-01	
C200099140	-	HOUSING.SAME AS 53013145 EXCEPT 2.089 +.002 -.000 WAS 2.123 +.002 -.000	
C200099141	-	HOUSING.SAME AS 553013146 EXCEPT 2.089 +.002 -.000 WAS 2.123	
C200099142	-	ROTOR SAME AS 551073117 EXCEPT SLEEVE 375002395 WAS .396	
C200099143	-	TEST PCS.FOR ENG.EVAL.VACUMET CONSUMET PURE IRON	
C200099144	-	DATA IDENT.-SAME AS C360160213 EXCEPT PART NO. TO BE CR40911062	
C200099145	-	KLEERGARD BEG-(TRIDENT)PER FOIL PK#6 MIL-B-131F CLASS2	
C200099146	-	INSERT MOLD ASSY.-SAME AS C200022220 EXCEPT ONLY 5 TERMINALS	
C200099147	-	MS 122 OLD RELEASE-TRIDENT MOLDS	
C200099148	-	INSUL.SLEEVING MIL-1-7444,TYPE 3,CLASS 1 COLOR CLASS 1 WHITE SIZE .208 LENGTH .75	
C200099149	-	THIXOGENOUS-GREASE MIX#3A(GRIT#500)YELLOW LABEL (WATER SOLUBLE) SILICON SKN CARBIDE	
C200099150	-	SAME C490194014 BRG.EXCEPT LUBE TO BE APIEZON OIL TYPE A (FISHER SCI.CO)	
C200099151	-	SAME AS C360165422 DATA IDENT.EXCEPT PART NO.TO BE CM41034103	
C200099152	-	SAME AS C490204014 BRG.EXCEPT LUBE TO BE APIEZON OIL TYPE A (PURCHASED FROM FISHER SCI.CO.)	
C200099153	-	BRG.SAME AS C491204310 EXCEPT OMIT LUBRICANT	
C200099154	-	ALUM.BLACK DYE FROM SANDOZE INC."CRO"	
C200099155	-	PILOT DIA.RING TO REPAIR HOUSING C305002258 HSG.	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099156	-	SAME AS A319A136-102 PIN K100A014	
C200099157	-	W.REDDICK	
C200099158	-		
C200099159	-	STACK FOR IDO#80-82-84453 SERVICE & REPAIR	
C200099160	-	LEAD WIRE BLACK PER RN#1Z350 & 1Z351 UT 36	
C200099161	A	LEAD WIRE RED PER RN#1Z350 & 1Z351 UT 36 SEE OPERATION SHEETS	27364
C200099162	-	PROTECTIVE MASK(TEFLON)SEE DET.1,2,3,4,6 OF A333A143-101 T77	
C200099163	-	C557002243 MAGNET CERAMIC PURCHASED BEFORE RN#113243	
C200099164	-	C200084248 HSG.MAGNET PURCHASED BEFORE RN#113243	
C200099165	A	PRECISION BRAND MAGNETIC SHIM STOCK .002 THICK 1-1/2"WIDE TOOL REF UA200A760-T003 (SEE OPERATION SHEETS)	55571
C200099166	-	SUPERSEDED BY NEW # 10500015	
C200099167	-	SUPERSEDED BY NEW # 10500016	
C200099168	-	ROTOR STACK FOR DEI#02799 .290 +.010 -.000 HIGH REF.C552052881	
C200099169	-	ROTOR LAM FOR DEI#02799 .010 +.001 -.001 THICK REF.C552002575	
C200099170	-	ROTOR & HUB FOR DEI#02799 C551075056	
C200099171	-	STATOR STACK FOR DEI#02799 .310 +.010 -.000 HIGH REF.C552052882	
C200099172	-	STATOR LAM FOR DEI#02799 .010 +.001 -.001 THK.REF.C552002572	
C200099173	-	STATOR & HSG.FOR DEI#02799 REF.C550075025	
C200099174	-	SAME AS C101105502 EXCEPT ON LOW LIMITS(.036-.042 OD)SUPPORT A333A865 TORQUER ASSY A201A412	
C200099175	-	INSULATOR FOR A200A763	
C200099176	-	MYLAR 1 MIL	
C200099177	-	MYLAR SHEET	
C200099178	-	MYLAR BAND-.001"X 1"	
C200099179	-	MYLAR BAND-.002"(.355 X 4.590)	
C200099180	-	SUPERSEDED BY NEW# 10 500 017	
C200099181	-	GEAR BLANK FOR CMO5715088 REF.310102009 & 310082711,712,713	
C200099182	-	GEAR BLANK FOR CMO5715088 REF.310102013 & 310082578	
C200099183	-	ROTOR SLEEVE(2)REQ'D TO USE AS 375022203-MADE FROM 375022202	
C200099184	-	SHAFT FOR C310130111 GEAR & SHAFT ASSY	
C200099185	-	HUB-C310140541 GERA CLUSTER,SPUR	
C200099186	-	HUB FOR C310140540 GEAR CLUSTER,SPUR	
C200099187	-	GEAR SHAFT C310170262 GEAR CLUSTER,SPUR	
C200099188	-	GEAR SHAFT C310170260	
C200099189	-	GEARSHAFT C310170258	
C200099190	-	Y113A002-440 MAG.WIRE FOR A506A025 (REF.IDO 51-82-20684)	
C200099191	-	A308A194-101 SPACER TORQ.COIL FOR A506A025 (REF.IDO 51-82-20684)	
C200099192	-	A506A025 COIL & SPACER (IDO 51-82-20684)	
C200099193	-	C550080432 STA.& HSG.REV.F.010 THK.LAMS CU09514004	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099194	-	C552052786 STATOR STACK	
C200099195	-	C552052797 STATOR STACK	
C200099196	-	C552052796 ROTOR STACK	
C200099197	-	C552052790 ROTOR STACK	
C200099198	-	INSULATION SLEEVING SAME AS Y110A005-050	
C200099199	-	STA.&HSG. SAME AS C550031504 EXCEPT PER DEI#02910	
C200099200	-	C550052011 EXCEPT OUTPUT WINDING IS INCREASED BY 4% (APPROX)	
C200099201	-	C550052015 EXCEPT OUTPUT WINDING IS INCREASED BY 4% (APPROX)	
C200099202	-	12K RESISTOR (RCL TYPE 7007(6,000RPM)REF.200062814 (NO DWG EXISTS)	
C200099203	-	13K RESISTOR (RCL TYPE 7007(6,000 RPM)REF.200062814 (NO DWG EXISTS)	
C200099204	-	HUB-SEE B.P C310140541	
C200099205	-	GEAR BLANK SEE B.P C310140541	
C200099206	-	HUB-SEE B.P C310140519	
C200099207	-	GEAR BLANK-GEAR "B"SEE BP.C310140519	
C200099208	-	GEAR SHAFT-SEE B.P C310170307	
C200099209	-	GEAR BLANK-SEE B.P C310170307	
C200099210	-	GEAR SHAFT-SEE B.P C310170307	
C200099211	-	GEAR BLANK "B"-SEE B.P C310170307	
C200099212	-	GEAR BLANK"A"-SEE B.P C310170307	
C200099213	-	GEAR BLANK"A"-SEE B.P C310140518	
C200099214	-	GEAR BLANK"B"-SEE B.P C310140518	
C200099215	-	GEAR BLANK"A"-SEE B.P C310140519	
C200099216	-	GEAR"B"-SEE B.P C310170309	
C200099217	-	GEAR SHAFT-SEE B.P C310170309	
C200099218	-	SHAFT SEE B.P C310170310	
C200099219	-	GEAR"B"-SEE B.P C310170310	
C200099220	-	GEAR "C" SEE B.P C310170310	
C200099221	-	GEAR "D" SEE B.P C310170310	
C200099222	-	SHAFT SEE B.P C310170311	
C200099223	-	GEAR"B" SEE B.P C310170311	
C200099224	-	GEAR"C" SEE B.P C310170311	
C200099225	-	SHAFT SEE B.P. C310170312	
C200099226	-	GEAR"B" SEE B.P C310170312	
C200099227	-	GEAR"C" SEE B.P C310170312	
C200099228	-	SHAFT SEE B.P. C310170313	
C200099229	-	GEAR"C" SEE B.P C310170313	
C200099230	-	SHAFT SEE B.P C310170314	
C200099231	-	HOBBED GEAR"B" SEE B.P C310170314	
C200099232	-	HOBBED GEAR "C" SEE B.P C310170314	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099233	-	GEAR HOBBED SEE B.P C310205024	
C200099234	-	GEAR HOBBED "A" SEE B.P C310205632	
C200099235	-	GEAR HOBBED "B" SEE B.P C310205632	
C200099236	-	GEAR "A" SEE B.P C310205832-835	
C200099237	-	GEAR "B" SEE B.P C310205832-835	
C200099238	-	GEAR "A" SEE B.P C310205847	
C200099239	-	GEAR "B" SEE B.P C310205847	
C200099240	-	GEAR "A" SEE B.P C310210125	
C200099241	-	GEAR "B" SEE B.P C310170313	
C200099242	-	GEAR "D" SEE B.P C310170312	
C200099243	-	SLEEING(MUL-I-7444 TYPE 3 CLASSI COLOR CLASS 1 WHITE SIZE .090(AWG 11)REF.200084750 10TB1	
C200099244	-	SLEEING(MUL-I-7444 TYPE 3 CLASSI COLOR CLASS 1 WHITE SIZE .090(AWG 11)REF.200084750 9TB1	
C200099245	-	SLEEING(MUL-I-7444 TYPE 3 CLASSI COLOR CLASS 1 WHITE SIZE .090(AWG 11)REF.200084750 8 TB1	
C200099246	-	SLEEING(MUL-I-7444 TYPE 3 CLASSI COLOR CLASS 1 WHITE SIZE .090(AWG 11)REF.200084750 7 TB1	
C200099247	-	SLEEING(MUL-I-7444 TYPE 3 CLASSI COLOR CLASS 1 WHITE SIZE .090(AWG 11)REF.200084750 6 TB1	
C200099248	-	BASE,MOTOR REPLACES 200083688	
C200099249	-	COMP.STATOR 200082292 WITH OLD DESIGN#552002459 LAM.	
C200099250	-	COMP.STACK 552052794 WITH OLD DESIGN#552002459 LAM.	
C200099251	-	TEFLON TEMPLATE(FOR PACKAGING)(OR HOLDER)A308A194-101(see paper copy for dwg/dimensions) NOTE RN 113554 - CM41014131 CALLS FOR C558042637 BR. BLOCK	
C200099252	-	SUPERSEDED BY NEW #10500037	
C200099253	-	SUPERSEDED BY NEW#10500018	
C200099254	-	BRUSH BLOCK SAME AS 558042613 EXCEPT LEADS TO BE 22"LONG *	
C200099255	-	GEAR BLANK TO BE USED WITH HUB C310110075	
C200099256	-	SUPERSEDED BY NEW#10500019	
C200099257	-	C553012907 HOUSING MODIFIED PER DEI-02906	
C200099258	-	C553013054 HOUSING MODIFIED PER DEI-02907	
C200099259	-	C550080431 STA.& HSG.PER DEI-02906	
C200099260	-	C550075048 STATOR&HOUSING PER DEI#02907	
C200099261	-	SUPERSEDED BY NEW# 10 500 020	
C200099262	-	STATOR & HOUSING ITEM#2 SAME AS C550080772 EXCEPT DE#02909	
C200099263	-	STATOR & HOUSING ITEM#3 SAME AS C550080772 EXCEPT DE#02909	
C200099264	-	STATOR & HOUSING ITEM#4 SAME AS C550080772 EXCEPT DE#02909	
C200099265	-	STATOR & HOUSING ITEM#5 SAME AS C550080772 EXCEPT DE#02909	
C200099266	-	SPEC.ROTOR-SAME AS C551073103 EXCEPT SLEEVE MAT'L GSK	
C200099267	-	GEAR FOR GEAR & HUB ASSY C310110332 GSK	
C200099268	-	A558A041-01 RETURN PATH & HOLDER ASSY	
C200099269	-	C552002506 LAM.(USING REV.A EXCEPT .014 THK) DEI-02912 & 02911	
C200099270	-	C552052787 STA.STK.(USING REV.A EXCEPT .014 THK)DEI-02912 & 02911	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099271	-	C550080431 STA.&HSG, WIND & IMPREG.TO C550072926 EXCEPT TURNS DEI-02912 & 02911	
C200099272	-	C550075048 STA.& HSG.WIND & IMPREG. TO C550072694 EXCEPT TURNS DEI-02912 & 02911	
C200099273	-	ROTOR C200082272 EXCEPT PER DEI#02906	
C200099274	-	ROTOR C551075048 EXCEPT PER DEI#02907	
C200099275	-	BRUSH HLDR. & RET.PATH ASSY-SAME AS A558A059-01(RN2G034-3)	
C200099276	-	RET.PATH-SAME AS A557A079-01 (RN2G034-3)	
C200099277	-	MAGNET-SAME AS A557A078-101 (RN2G034-3)	
C200099278	-	BR.& HOLDER ASSY-SAME AS A558A058-01 (RN2G034-3)	
C200099279	-	SUPPORT BRUSH-SAME AS A359A016-101 (RN2G034-3)	
C200099280	-	Y105A003-101(DC RTV 732 SILASTIC) FOR DEI#02906	
C200099281	-	RETURN PATH MAG.ASSY-SAME AS A557A043-01 EXCEPT USE 10 500 034 MAGNETS	
C200099282	-	RETURN PATH MAG.ASSY-SAME AS A557A043-01 EXCEPT USE 10 500 034 MAGNETS	
C200099283	-	HOUSING FOR CX40195132-7 ORG.MADE C553013116	
C200099284	-	HOUSING C553013115 END UNIT CX40195136	
C200099285	-	ROTOR SUB-USED ON 9R915-01H-D	
C200099286	-	ROTOR-USED ON 9R915-01H-D	
C200099287	-	SLEEVE ROTOR-SAME AS C375022373 NEW STOCK ROLLED	
C200099288	-	ROTOR FOR CT40192008 USING ABOVE SLEEVE(CARPENTER#49 MAT'L)	
C200099289	-	THOMPSON LAM 2096VR8S621.SIMILAR:552002601 DEI#02917 SOMMERVILLE	
C200099290	-	C551072660 ROTOR MODIFIED PER NOTE#1 DEI#01238	
C200099291	-	C551072660 ROTOR MODIFIED PER NOTE#3 DEI#01238	
C200099292	-	SHAFT SAME AS C340012462 EXCEPT-SEE "Q" FORM	
C200099293	-	SHAFT SAME AS C340002171 EXCEPT-SEE "Q" FORM	
C200099294	A	LEAD WIRE IAW MIL-W-22759/18-24-92 (WHT-RED)	85533
C200099295	A	LEAD WIRE IAW MIL-W-22759/18/24/90 (WHT-BLK)	85533
C200099296	A	LEAD WIRE IAW MIL-W-22759/18/24/936 (WHT-ORN-BLU)	85533
C200099297	A	LEAD WIRE IAW MIL-W-22759/18-24-934 (WHT-ORN-YEL)	85533
C200099298	A	LEAD WIRE IAW MIL-W-22759/18/24/903 (WHT-BLK-ORN)	85533
C200099299	A	LEAD WIRE IAW MIL-W-22759/18-24-923 (WHT-RED-ORN)	85533
C200099300	-	SHAFT-(SAME AS 231106 EXCEPT SHAFT EXT.D.A.)	
C200099301	-	ROTOR SUB-(SAME AS 326234 EXCEPT SHAFT)	
C200099302	-	ROTOR-(SAME AS C551072342 EXEPT)-(IDO#80-82-89548)	
C200099303	-	ROTOR SUB-(SAME AS C551062425 EXCEPT-)(IDO#80-82-89548)	
C200099304	-	SHAFT-(PER CU09608006) (IDO#80-82-89548)	
C200099305	-	GEAR BLANK 310100213 MARCO C310110241	
C200099306	-	310100213 GEAR USE ON C310990236 GEAR SPUR FREE	
C200099307	-	310140062 GEAR USE ON C310140062	
C200099308	-	310100001 GEAR BLANK C310140061 GEAR CLUSTER MARCO	
C200099309	-	310100034 GEAR BLANK C310080176 GEAR SHAFT ASSY	



# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099310	-	310100213 GEAR BLANK C310110134 GEAR & HUB ASSY	
C200099311	-	310109025 GEAR BLANK C310110133 GEAR & HUB ASSY	
C200099312	-	C310100175 GEAR A C310110131 GEAR & HUB ASSY	
C200099313	-	C310100175 GEAR B C310110131 GEAR & HUB ASSY	
C200099314	-	ROTOR STOCK REF.C375022180 EXCEPT ROLLED 49FM DEI#01237	
C200099315	-	SHAFT FOR C310170256-1 PC CONSTRUCTION	
C200099316	-	SHAFT FOR C310170232 PC CONSTRUCTION	
C200099317	-	SHAFT FOR C310170267 PC CONSTRUCTION	
C200099318	-	SLEEVE FOR SPEC.C551073117 CY40195104	
C200099319	-	ROTOR FOR SPEC.C551073117 CY40195104	
C200099320	-	#39 GA.WIRE-SAME AS C101006123 EXCEPT RESIST.TO BE 8.00-8.30	
C200099321	-	STAINLESS STEEL WASHER-THK.030-ID .059-OD .750 STA.&HSG.	
C200099322	-	LAPPING GEAR FOR CU09609077-078	
C200099323	-	DEI#1242 A552A023 LAM ASSY	
C200099324	-	DEI#1242 A314A154 HOUSING	
C200099325	-	DEI#1242 A200A763-01 ARMATURE TORQUER ASSY	
C200099326	-	WINDING RETAINER FOR STATOR&HOUSING #550031287 (PER D.HOEFLING)	
C200099327	-	INSULATOR FOR A200A763-SMALL TORQUER	
C200099328	-	GEAR SHAFT ASSY C310087082 (SHAFT)	
C200099329	-	SAME AS C307002227 EXCEPT USE 303 S.S.	
C200099330	-		
C200099331	-	SAME AS C551075057 ROTOR EXCEPT .160 SLOT PAPER & PRE SHRUNK LACING TAPE	
C200099332	-	REWORKED 343022477 RETAINER FOR ECONOLINE	
C200099333	-	ROLLED STOCK FROM GROB ANNEALED REF.375022373	
C200099334	-	ROLLED STOCK FROM GROB HOT ANNEALED REF.375022373	
C200099335	-	ROTOR USING SLEEVE 200099333 REF.551071519	
C200099336	-	ROTOR USING SLEEVE 200099334 REF.551071519	
C200099337	-	WINDING RETAINER FOR STATOR & HSG.#550031287	
C200099338	-	Y113A005-101 MAG.WIRE TO BE USED ON TORQUER CUP	
C200099339	-	Y105A017 P.D GEORGE PEDIGREE #946	
C200099340	-	SAME AS C101006128 EXCEPT DCR 26.65-23.52 OHMS FOR 10 FT.LENGTH AT 20 DEGREE C+GEN DYE	
C200099341	-	A314A105 NEW PROCESS TO BE RE-IDENTIFIED UPON COMPLETION	
C200099342	-	SAME AS C310002284 EXCEPT T.R IS .0005 SMALLER	
C200099343	-	SAME AS C200083435 EXCEPT USES 200099342 GEAR	
C200099344	-	PENDULUM & SHAFT ASSY(COMBINED PART #'S 200083085 & 200083086)FOR CANT ANGLE SENSOR	
C200099345	-	553013104 BUT 2.000+.010 -.010 DIA. IS 2.010 +.010 -.010 AND 30' MAX TAPER	
C200099346	-	553013107 BUT 2.000+.010 -.010 DIA.IS 2.010 +.010-.010 AND 30' MAX TAPER	
C200099347	-	553013104 15'MAX TAPER IS 30' MAX TAPER	
C200099348	-	553013107 BUT 2.000+.010 -.010 DIA.IS 2.010 +.010-.010 AND 30' MAX TAPER	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099349	-		
C200099350	-	200099345 MACHINED TO 553013187 DRAWING	
C200099351	-	200099346 MACHINED TO 553013188 DRAWING	
C200099352	-	200099347 MACHINED TO 553013216 DRAWING	
C200099353	-	200099348 MACHINED TO 200099283 DRAWING	
C200099354	-	SIZE 15 BENDIX IMPREG.WITH SCOTCHCAST-8 ONLY	
C200099355	-	C300002162 & C300002179 JIG BORED MATCHED SET	
C200099356	-	STACK FOR "Q"FORM-SAME AS 200019549 EXCEPT USE EPON 828 ADHESIVE C180000481	
C200099357	-	SAME AS A508A011 EXCEPT USING 36 1/2 GA.WIRE C101006119 DEI#01250	
C200099358	-	SAME AS A200A763 EXCEPT OMIT SLOT WEDGES AND MACHINING STACK FACE	
C200099359	-	780780-11-SHAFT AL.SUM.	
C200099360	-	D780783-04 ROTOR AL.SUM.	
C200099361	-	FOR C200089822 END BELL	
C200099362	-	FOR C200089821 LAM & CSTING ASSY	
C200099363	-	#37 GA.WIRE-SAME AS C101006120 EXCEPT RES. TO BE 4.901-5.05 OHMS/10 FT.@20 DEGREE C	
C200099364	-	#35 GA.WIRE-SAME AS C101006116 EXCEPT RES.TO BE 3.192-3.269 OHMS/10 FT@20 DEGREE C	
C200099365	-	SLUG FOR C200086550(MOLD MAT'L C101063013)	
C200099366	A	LEAD WIRE IAW MIL-W-22759/18-24-4 (YELLOW) SEE OPERATION SHEETS	78509
C200099367	A	LEAD WIRE IAW MIL-W-22759/18-24-6 (BLUE) SEE OPERATION SHEETS	78509
C200099368	-	FORMING FIXTURE FOR A200A763-01 EXPERIMENTAL FIXTURE	
C200099369	-	COVER;SEE"Q"FORM CV90160008 FOR DETAILS	
C200099370	-	SHAFT;SEE"Q"FORM CV90160008 FOR DETAILS	
C200099371	-	SAME AS A508A011 EXCEPT USE 39 TURNS OF 36 1/2 AWG SINGLE NYLEZE DEI#01252	
C200099372	-	SAME AS A200A763 EXCEPT USE 50 TURNS OF 38 1/2 AWG SINGLE NYLEZE DEI#01253	
C200099373	-	SAME AS A200A766 EXCEPT USE 53 TURNS OF 34 1/2 AWG SINGLE NYLEZE DEI#01254	
C200099374	-	SAME AS C553013146 EXCEPT BORE HSG.	
C200099375	-	SAME AS C553013145 EXCEPT BORE HSG.	
C200099376	-	SAME AS C375002396 EXCEPT MAT'L:B112 SLEEVE	
C200099377	-	SAME AS C551073117 EXCEPT ROTOR	
C200099378	-	ROTOR ASSY-SAME AS A551A007-01 XM1	
C200099379	-	ROTOR SUPPORT-SAME AS A333A921-101 XM1	
C200099380	-	ROTOR LAM-SAME AS A552A039-101 XM1	
C200099381	-	STATOR ASSY-SAME AS A550A021 XM1	
C200099382	16	STATOR LAM.ASSY FOR A550A021 (19 A552A040-101 LAMS)	79539
C200099383	-	ROTOR SPEC.C551073117 EXCEPT SLEEVE	
C200099384	-	ROTOR SLEEVE SPEC. C375002396 EXCEPT TEETH WIDTH	
C200099385	-	SUPPORT-TORQUER A333A922	
C200099386	-	SAME AS A202A074-01	
C200099387	-	SHAFT 340013273 MODIFIED PER N.J. (DAVE W.)	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099388	-	SUPPORT-ROTOR A333A921-101	
C200099389	-	C310072730 EXCEPT T.R.IS .0005 LARGER	
C200099390	-	C310072732 EXCEPT T.R. IS .0005 LARGER	
C200099391	-	SAME AS A314A154 EXCEPT S.S.416-CONOA	
C200099392	-	SAME AS A558A059 EXCEPT USING ALNICO V IN PLACE OF V-7	
C200099393	-	SAME AS A557A078 EXCEPT USING ALNICO V IN PLACE OF V-7	
C200099394	-	PENDULUM & SHAFT	
C200099395	-	SAME AS A557A043 EXCEPT USING ALNICO V IN PLACE OF V-7	
C200099396	-	SAME AS A557A037 EXCEPT USING ALNICO V I PLACE OF V-7	
C200099397	-	SAME AS A557A041 EXCEPT ALNICO V MAGNETS	
C200099398	-	SAME AS A557A042 EXCEPT ALNICO V	
C200099399	-	SAME AS A511A199-101	
C200099400	-	8" X8" FOAMVELOPE FOR CHRYSLER XM1 PACKING	
C200099401	-	6" X 6" FOAMVELOPE FOR CHRYSLER XM1 PACKING	
C200099402	-	4" X 4" FOAMVELOPE FOR CHRYSLER XMI PACKING	
C200099403	-	IDO 80-82-91322 PHASE 1 GSK	
C200099404	-	SHAFT FOR "Q" FORM SAME AS 340002709 EXCEPT EXT.	
C200099405	-	RETAINER DUST SEAL BENDIX SIZE 11,GEARHEAD	
C200099406	-	LAM 552002601 BUT .621 I.D	
C200099407	-	STACK 552052894 BUT MADE WITH 200099406 LAM	
C200099408	-	A201A515-101 PICK-OFF CORE	
C200099409	-	GEAR & ARMATURE ASSY	
C200099410	-	552002601 LAM BUT NO ANNEALING	
C200099411	-	300 ROTOR ASSY	
C200099412	-	ROTOR WITH 340013429 SHAFT MADE FROM 303 S.S	
C200099413	-	ENDBELL FOR ("Q" FORM UNIT)	
C200099414	-	BEARING 311012108 BUT MADE OF GARLOC'S MULTILUBE	
C200099415	-		
C200099416	-	ROTOR REF.551073276 ROTOR MAT'L REVIEW#026	
C200099417	-	STA.& HSG. FOR CX40195153-SPECIAL LEADS	
C200099418	-	SAME AS C310002284 EXCEPT T.R. IS .2176 +.0000 -.0003	
C200099419	-	SAME AS C200083435 EXCEPT USE GEAR 200099418	
C200099420	-	INNER PLATE (300002179)	
C200099421	-	OUTER PLATE (300002162)	
C200099422	-	CASTING SAME AS 333002588 EXCEPT DEI#01262	
C200099423	-	CASTING MACHINED-SAME AS 333002589 EXCEPT DEI#01262	
C200099424	-	SAME AS 550052526 EXCEPT USED 200019423 DEI#01262	
C200099425	-	SAME AS 550052894 EXCEPT LAMS USED ARE UNANNEALED	
C200099426	-	A200A763-HAS S.S. 416 HOUSING	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099427	-	RAYCHEM #202 & 211 SLEEVING(FOR C200086537 & C200086538)	
C200099428	-	SHAFT FOR "Q" FORM UNIT	
C200099429	-	ROTOR 551073117 BUT O.D. .6210 +.0005 -.0000	
C200099430	-	STATOR,C550070811-O.D. 1.796-1.7965 PER DEI#01265	
C200099431	-	ARMATURE HSG.ASSY B200041514-1 1.8095-1.810 PER DEI#01265	
C200099432	-	SHAFT FOR "Q"FORM "D" SIZE B/P ASS'Y	
C200099433	-	END BELL FOR "Q"FORM-FORM"D" SIXE B/P ASS'Y	
C200099434	-	MOUNTING BRACKET(PAINTED) REF.3-630050-02	
C200099435	-	INSULATOR FOR "Q"FORM SAME AS C511002192 EXCEPT 1.425 O.D.	
C200099436	-	HOUSING-REF.553013114 AS PER AL SUMMERVILLE	
C200099437	-	SAME AS 552002546 EXCEPT .006 THK LAM	
C200099438	-	SAME AS 552002545 EXCEPT .006 THK LAM	
C200099439	-	SAME AS 552052879 EXCEPT .006 THK LAM (STACK)	
C200099440	-	SAME AS 552052880 EXCEPT .006 THK LAM (STACK)	
C200099441	-	SAME AS 550075057 EXCEPT MAGNET WIRE #42 & .006 LAM	
C200099442	-	SAME AS 550075026 EXCEPT MAGNET WIRE #42 & .006 LAM	
C200099443	-	SAME AS 551075057 EXCEPT MAGNET WIRE #42 & .006 LAM	
C200099444	-	SAME AS 310013126 EXCEPT DEI#02937	
C200099445	-	SAME AS 310072653 EXCEPT DEI#02937	
C200099446	-	SAME AS 310013129 EXCEPT DEI#02937	
C200099447	-	SAME AS 310072657 EXCEPT DEI#02937	
C200099448	-	SAME AS 310072658 EXCEPT DEI#02937	
C200099449	-	SAME AS 310013131 EXCEPT DEI#02937	
C200099450	-	SAME AS 310072678 EXCEPT DEI#02937	
C200099451	-	ARMATURE WITH REGULAR HOUSING & SPECIAL WINDING-DEI#01264	
C200099452	-	SAME AS C552002464 EXCEPT DEI#02940	
C200099453	-	SAME AS C552052754 EXCEPT DEI#02940	
C200099454	-	SAME AS C557072017 EXCEPT DEI#02940	
C200099455	-	SAME AS C550080232 EXCEPT DEI#02940	
C200099456	-	SAME AS C550070824 EXCEPT DEI#02940	
C200099457	-	DEI# S&H SAME AS 550080021 EXCEPT LONGER STACK	
C200099458	-	DEI# STACK SAME AS 552052293 EXCEPT (2) LAMS LONGER	
C200099459	-	SAME AS 551072302 EXCEPT .4975 +.0000 -.0002 DIA (10 PCS)	
C200099460	-	ARMATURE WITH REGULAR HOUSING AND SPECIAL WINDING-DEI#01263	
C200099461	-	WINDING FORM (MOLDED)DEI#----(SEE D.HOEFLING)	
C200099462	-	GEAR BLANK FOR CM05715088 (REF.310102009)	
C200099463	-	SAME AS C550070193 STATOR EXCEPT DEI#02944	
C200099464	-	SAME AS C550080442 S&H EXCEPT DEI#02944	
C200099465	-	SAME AS C551073322 EXCEPT WIND PER DEI#02945	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099466	-	SAME AS C552002464 EXCEPT DEI#02946	
C200099467	-	SAME AS C550070811 EXCEPT PER DEI#01269	
C200099468	-	SAME AS B200041573-1 EXCEPT PER DEI#01267	
C200099469	-	SAME AS B200041514-1 EXCEPT PER DEI#01268	
C200099470	-	OBSOLETE:SUPERSEDED NY N.J.#C527002218 (B.L 5/12/80)	
C200099471	-	SAME AS C550070193 STATOR EXCEPT DEI#02950	
C200099472	-	SAME AS C550080442 STA.& HSG.EXCEPT DEI#02950	
C200099473	-	STATOR,C550070811-O.D. 1.796-1.7965 PER DEI#01265	
C200099474	-	SAME AS C550080467 EXCEPT DEI#02949	
C200099475	-	SAME AS C550070193 EXCEPT DEI#02941	
C200099476	-	SAME AS C550080442 EXCEPT DEI#02941	
C200099477	-	SAME AS C550070193 EXCEPT DEI#02947	
C200099478	-	SAME AS C550080442 EXCEPT DEI#02947	
C200099479	-	SAME AS CR40192024 EXCEPT DEI#02953	
C200099480	-	SAME AS C550070193 EXCEPT DEI#02953	
C200099481	-	SAME AS C550080442 EXCEPT DEI#02953	
C200099482	-	SAME AS C550080442 EXCEPT DEI#02951	
C200099483	-	SAME AS C550070193 EXCEPT DEI#02951	
C200099484	-	SAME AS C552052910 EXCEPT DEI OX INSUL.	
C200099485	-	SAME AS C552052911 EXCEPT DEI OX INSUL.	
C200099486	-	SAME AS C552002568 EXCEPT DEI OX INSUL.	
C200099487	-	SAME AS C552002569 EXCEPT DEI OX INSUL.	
C200099488	-	SAME AS C333002272 EXCEPT(SEE SOA#A937)(USE IN INNER STA. C550052389 & 385)	
C200099489	-	STACK SAME AS C552052754 EXCEPT PER DEI#02946 (DELCO)	
C200099490	-	STA.& HSG. SAME AS C550080232 EXCEPT PER DEI#02946 (DELCO)	
C200099491	-	STATOR & HSG. SAME AS C550080875 EXCEPT PER DEI# (MTS)	
C200099492	-	ROTOR SAME AS C551073251 EXCEPT PER DEI# (MTS)	
C200099493	-	R.STACK SAME AS C552052917 EXCEPT PER DEI# (MTS)	
C200099494	-	S.STACK SAME AS C552052922 EXCEPT PER DEI# (MTS)	
C200099495	-	CHIP FOR PART#307002303 O BROACH GSK	
C200099496	-	VARISOL FOR CLEANING SCREENS ON TSCHUDIN PN C550075025 #2131 TRIDENT OP#655	
C200099497	-	C550070193 STATOR EXCEPT DEI#02959	
C200099498	-	SAME AS C553012929 EXCEPT 8 MOUNTING HOLES	
C200099499	-	SAME AS 200082529 HSG-PLATE EXCEPT 8 HOLES IN MTG. DIA. ORDER NO.80-8294878	
C200099500	-	SAME AS 550080771 EXCEPT A-B T/C,C-13 T/C	
C200099501	-	ELECTRO ETCH CLEANER FORMULA #2	
C200099502	-	ELECTRO ETCH 2611A	
C200099503	-	LUSOL "G"	
C200099504	-	TRI-X-100	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099505	-	COMP D	
C200099506	-	S-16 STRIPPER FOR EPOXY	
C200099507	-	KESTER 196 SOLDER FLUX	
C200099508	-		
C200099509	-	TOLUENE	
C200099510	-	METHYL CELLUSOLVE	
C200099511	-	ARROW BLAST REF.200079239 (REGULAR PRODUCTION)	
C200099512	-	CAB-O-SIL MS	
C200099513	-	C553013256 HOUSING-MADE FROM FORGING	
C200099514	-	SAME AS C552052386 STATOR STACK EXCEPT O.D.GROUND AS A STA.& HSG.	
C200099515	-	SAME AS A314A376-01 GYRO HSG	
C200099516	-	OBSOLETE-SEE 200099602	
C200099517	-	SHAFT FOR "Q"FORM	
C200099518	-	MATCHED SET IC & RESISTOR	
C200099519	-	SAME AS C550042068 S&H EXCEPT 19-STRAND LEAD WIRE	
C200099520	-	SAME AS C558042172 BRUSH BLOCK EXCEPT 19-STRAND LEAD WIRE	
C200099521	-	A508A019-101 PICKOFF CORE (IMPROVED CONEX)	
C200099522	-	A202A267-01 PICKOFF & COIL ASS (IMPROVED CONEX)	
C200099523	-	A202A265-01 TORQUER & COIL ASSY (IMPROVED CONEX)	
C200099524	-	A202A266-01 HSG.& TORQUER ASSY (IMPROVED CONEX)	
C200099525	-	A544A981-101 PT'D CABLE ASSY (IMPROVED CONEX & XMI)	
C200099526	-	A506A038-101 BOBBIN COIL (IMPROVED CONEX & XMI)	
C200099527	-	A201A513-01 PICKOFF & COIL ASSY (XM1)	
C200099528	-	A201A512-01 TORQUER & COIL ASSY (XM1)	
C200099529	-	A201A510-01 HSG.& TORQUER (XM1)	
C200099530	-	A314A253-01 HSG.GYRO SCOPE (XM1 & IMPROVED CONEX)	
C200099531	-	MOLDING MAT'L 1907 BLACK	
C200099532	-	STACK-SAME AS C552052933 EXCEPT PER DEI#	
C200099533	-	INSULATED STACK ASSY-SAME AS C200086495 EXCEPT PER DEI#	
C200099534	-	STATOR ASSY-SAME AS 550074252 EXCEPT PER DEI#	
C200099535	-		
C200099536	-	STA.& HSG.-SAME AS 550080902 EXCEPT PER DEI#	
C200099537	-	STACK-SAME AS 552052913 EXCEPT PER DEI#	
C200099538	-	INSULATED STACK ASSY-SAME AS C200086599 EXCEPT PER DEI#	
C200099539	-	STATOR ASSY-SAME AS 550074294 EXCEPT PER DEI#	
C200099540	-	STA.& HSG.-SAME AS 550080935 EXCEPT PER DEI#	
C200099541	-	STA.& HSG.-550080746 EXCEPT 235 TURNS-#33 M.W.	
C200099542	-	STATOR-SAME AS 550070193 EXCEPT PER DEI#02963	
C200099543	-	STA.&HSG.ASSY-SAME AS C550080442 EXCEPT DEI#02963	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099544	-	STATOR-SAME AS 550070193 EXCEPT DEI#02964	
C200099545	-	STA.& HSG.-SAME AS 550080442 EXCEPT DEI#02964	
C200099546	-	BEARING-SAME AS 200084951 EXCEPT RADIAL PLAY & LUBE	
C200099547	-	BEARING-SAME AS 200084951 EXCEPT RADIAL PLAY & LUBE	
C200099548	-	ROTOR SLEEVE-375022258 EXCEPT MILLED TEETH & A.I.S.I. 12L14 STEEL	
C200099549	-	ROTOR HUB ASSY-C200086278 EXCEPT DEI#01270	
C200099550	-	STATOR HOUSING ASS'Y-C550080863 EXCEPT DEI#01270	
C200099551	-	ROTOR STACK FOR DEI#01278(SKEW ANGLE .131 +.003 -.003)(CHRYSLER BX)	
C200099552	-	ROTOR SUB FOR DEI#01278(SKEW ANGLE .131 +.003 -.003)(CHRYSLER BX)	
C200099553	-	ROTOR FOR DEI#01278(SKEW ANGLE)(CHRYSLER BX)	
C200099554	-	SWEN 251 REF.P/N 780-032 (WAS BENDIX 25I)	
C200099555	-	REAGENT METHANOL REF.Y102A004	
C200099556	-	STEPPER MOTOR-SAME AS CR4019-024 EXCEPT DEI#02964	
C200099557	-	STEPPER MOTOR-SAME AS CR4019-024 EXCEPT DEI#02963	
C200099558	-	HOUSING-SAME AS C553013359 EXCEPT 1.090-1.084 TO BE 1.064-1.058 RN#117531	
C200099559	-	ROTOR-SAME AS 780-783-01 EXCEPT SILVER EPOXY BOND	
C200099560	-	ROTOR STACK FOR DEI#01278(SKEW ANGLE=.141 +.003 -.003) XM1 (8X)	
C200099561	-	ROTOR SUB FOR DEI#01278(SKEW ANGLE=.141 +.003 -.003) XM1 (8X)	
C200099562	-	ROTOR FOR DEI#01278	
C200099563	-	ROTOR STACK FOR DEI#01278(SKEW ANGLE=.151 +.003 -.003)XM-1 (8X)	
C200099564	-	ROTOR SUB FOR DEI#01278(SKEW ANGLE .151 +.003 -.003) XM-1 (8X)	
C200099565	-	ROTOR FOR DEI#01278(SKEW ANGLE .151 +.003 -.003)XM-1 (8X)	
C200099566	-	SUPPORT EXP BENDIX .005 +/- HERMETIC LASER SEAL	
C200099567	-	HOUSING EXP BENDIX .005 +/- HERMETIC LASER SEAL	
C200099568	-	LEAD SCREW SHAFT REF. 340013443 GSK	
C200099569	-	BUSHING-REF. 2-636189-01 GSK	
C200099570	-	STATOR STACK(C552052922 DEI#01281) J.A.S.	
C200099571	-	STATOR STACK(C552052923 DEI#01281)	
C200099572	-	STA.& HSG.(550080875 DEI#01281)	
C200099573	-	STA.& HSG.(C550080877 DEI#01281)	
C200099574	-	STA.& HSG.(C550080876 DEI#01281)	
C200099575	-	STA.& HSG.(C550080874 DEI#01281)	
C200099576	-	SUPPORT(A333A921-101 DEI#01282)(PROCEDURE #1) ECK	
C200099577	-	ROTOR ASS'Y (A551A007-01 DEI#01282)(PROCEDURE #1)	
C200099578	-	SUPPORT (A333A921-101 DEI#01282) (PROCEDURE #2) ECK	
C200099579	-	ROTOR ASS'Y (A551A007-01 DEI#01282)(PROCEDURE #2)	
C200099580	-	SUPPORT STATOR REF.333002626 GSK	
C200099581	-	HOUSING REF.553013355 GSK	
C200099582	-	WASHER REF.ABOVE GSK	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099583	-	LAMINATION ASS'Y REF. DEI#01282 (PROCEDURE#2) ECK	
C200099584	-	ARMATURE-SAME AS A200A763-01 EXCEPT BORE AT OP#80(DEI#01283) CAL	
C200099585	-	SAME AS C557002115 EXCEPT 21 ON TESTER(USE ON C200052557 MAG:HSG.-CU09611033 ONLY)	
C200099586	-		
C200099587	-		
C200099588	-	ENGR.SKETCH OF 200087213(TERMINAL,BENDIX HERM-SEAL STEPPER)	
C200099589	-	SAME AS 310072677 EXCEPT TESTING RADIUS .0003 ABOVE B/P	
C200099590	-	SAME AS 310072678 EXCEPT TESTING RADIUS .0003 ABOVE B/P	
C200099591	-	BOBBIN(FOR MACOR COIL & BOBBIN ASSY)P/N A506A062-01	
C200099592	-	MACOR COIL & BOBBIN P/N A506A063-01	
C200099593	-	Y113A010-101 C#44 NYLEZE MAG.WIRE MACOR COIL & BOBBIN	
C200099594	-	SAME AS 551073266 ROTOR EXCEPT RING DIMENSIONS	
C200099595	-	SAME AS 310002910 GEAR EXCEPT SPECIAL COATING	
C200099596	-	SAME AS 200086454 ARMATURE EXCEPT SPECIAL MACHINING	
C200099597	-	SAME AS 551073266 EXCEPT GROOVED ROTOR	
C200099598	-	SAME AS 200087121 EXCEPT COIL SPRINGS	
C200099599	-	SAME AS 310148011 EXCEPT COIL SPRINGS	
C200099600	-	SAME AS 551062889 EXCEPT COATED WITH ARMSTRONG 8155	
C200099601	-	SAME AS #553013286 XM-1 HSG. EXCEPT FORGED HSG.BLANK	
C200099602	-	SAME AS #554002913 XM-1 END BELL EXCEPT FORGED E.B.BLANK	
C200099603	-	CABLE ASSY FOR 12281140(C536002363)	
C200099604	-	ROTOR-551073356 REFERENCE SPEC.SHAFTS	
C200099605	-	SHAFT FOR ABOVE ROTOR	
C200099606	-	RANDOM SAMPLE OF LAMS FOR LASER STACK WELD FEASIBILITY	
C200099607	-	553013223 SHORTENED BY 3/16"	
C200099608	-	553013224 SHORTENED BY 3/16"	
C200099609	-	551073356 ROTOR WITH 5/8"LONG SLEEVE	
C200099610	-	LAM SAME AS 552002670 EXCEPT I.D..369 +.001 -.000	
C200099611	-	LAM STACK 552052977 EXCEPT PUNCH FROM DANCO & GROUND	
C200099612	-	P.M.SLUG FOR FRONT HOUSING	
C200099613	-	P.M.SLUG FOR REAR HOUSING	
C200099614	-	SAME AS C550031504 STA.&HSG.EXCEPT (3 MIN.ERROR UNITS)	
C200099615	-	C553012731 HSG.WITH FINISHED MTG.DIM'S(STA.& HSG.ON H-52 3 UNITS)	
C200099616	-	SHAFT LIKE C340012171 EXCEPT PER "Q"FORM FOR MODIFICATION	
C200099617	-	552052898 STACK BUT 5/8" LONG	
C200099618	-	550080746 WITH SHORT HSG.&STACK & 333 TURNS GA.#34 WIRE	
C200099619	-	550080746 WITH SHORT HSG.& STACK & TBD	
C200099620	-	SAME AS C552052696 EXCEPT SUNEN HONE I.D	
C200099621	-	SAME AS 642AS8400-1 FOR ACCOUNTING	



# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099622	-	SAME AS 642AS8400-2 FOR ACCOUNTING	
C200099623	-	320002867 EXCEPT NICKEL PLATE	
C200099624	-	320002868 EXCEPT NICKEL PLATE	
C200099625	-	SHIM-O.D=.860+.005 -.005,ID=.750 +.005 -.005,.085 +.005 -.005 THICK;416 S.S.	
C200099626	-	ROTOR SLEEVE 375022255 BUT WITH I.D.HONED	
C200099627	-	ROTOR SHAFT FOR 200099626 SLEEVE	
C200099628	-	ROTOR ASS'Y OF 200099626 & 627	
C200099629	-	STATOR & HSG.-LIKE S&H FOR CX40195132 BUT DIFFERENT WDG.	
C200099630	-	STATOR-CU40194049 DETAIL 6-6 MADE FOR N.J.-SOA#A2947	
C200099631	-	SPECIAL SLEEVE FOR HERM.SEAL THRU BORE	
C200099632	-	SAME AS C333002626 EXCEPT THRU BORE	
C200099633	-	SAME AS 551073428 ROTOR EXCEPT HUBBED SLEEVES	
C200099634	-	FRONT HSG.1836 STEPPER .002 LESS ON M.S.	
C200099635	-	REAR HSG. 1836 STEPPER .002 LESS ON M.S.	
C200099636	-	VARIABLE RELUCTANCE ROTOR	
C200099637	-	STA.& HSG. FOR SIEMENS PROTOTYPE 135 T/C OF 200052020	
C200099638	-	STA.& HSG. FOR SIEMENS PROTOTYPE 150 T/C OF 200052021	
C200099639	-	ROTOR SLEEVE FOR SIEMENS PROTOTYPE	
C200099640	-	B200041514-1 WITH 200099641 LAM.ASS'Y DEI#01285	
C200099641	-	C552051042 EXCEPT O.D.TO BE 2.2055/2.205 DEI#1295	
C200099642	-	SAME AS C550031502 STA.& HSG. EXCEPT HSG.HAS FINISH MTG,DIA. 3 MIN.ERROR	
C200099643	-	SAME AS C550031506 STA.& HSG. EXCEPT HSG.HAS FINISH MTG,DIA. 3 MIN.ERROR	
C200099644	-	SAME AS C550080992 EXCEPT STATOR 550080442 CONFIGURATION	
C200099645	-	SAME AS 550080990 EXCEPT USE HAND INSERTED STATOR	
C200099646	-	SLEEVE FROM"Q"-FORM CT00174003	
C200099647	-	MATCHED SET (R1,R3,U5)	
C200099648	-	SAME AS 375022257 EXCEPT FORMED STOCK	
C200099649	-	SAME AS 551073356 EXCEPT SLEEVE AS ABOVE	
C200099650	-	ROTOR ASSY A551A007-01 ON DEI#01297	
C200099651	-	STACK ASS'Y FOR ABOVE	
C200099652	-	STACK ASS'Y FOR PROGRAM 1836 FOR WINDING TRIAL	
C200099653	-	STATOR FOR PROGRAM 1836 FOR WINDING TRIAL	
C200099654	-	VACUUM SCHMELTZER MAGNETS FOR ROTORS	
C200099655	-	ROTORS WITH 200099654 MAGNETS	
C200099656	-	ROTOR SLEEVES LIKE 375022207 BUT MADE OF 375022168	
C200099657	-	ROTOR SHAFT MADE FROM 340013442	
C200099658	-	ROTOR MADE OF 200099657 SHAFT& .656 SLEEVE ETC.	
C200099659	-	ROTOR MADE OF 200099657 SHAFT AND 375022207 SLEEVE	
C200099660	-	SHAFT SPACER FOR ABOVE 2 ROTORS	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099661	-	STATOR SUPPORT AND TERMINAL ASS'Y USING C200099632 SUPPORT	
C200099662	-	STATOR & SUPPORT ASS'Y USING C200099661 SUPPORT ASS'Y	
C200099663	-	CENTER TAP STATOR FOR PROGRAM 1836	
C200099664	-	DEI#S FOR 200086495 XM-1 MOLDED STACK DM	
C200099665	-	ROTOR SUB S/A C551052502 EXCEPT USE SHAFT C340010558	
C200099666	-	552052977 STACK 1.9580 +.0000 -.0002	
C200099667	-	200086599 XM-1 MOLDED STACK ASS'Y	
C200099668	-	SAME AS C550080902 EXCEPT USE 200099664 STACK	
C200099669	-	SAME AS C550080935 EXCEPT USE 200099667 STACK	
C200099670	-	MAG ASS'Y FOR CR41304001	
C200099671	-	CU40196101 STACK-UNGROUND	
C200099672	-	CU40196101 STATOR WITH UNGROUND STACK	
C200099673	-	CU40196101 FRONT HSG.FOR LOOSE FIT TO UNGROUND STACK	
C200099674	-	CU40196101 REAR HSG.FOR LOOSE FIT TO UNGROUND STACK	
C200099675	-	CU40196101 FRONT HSG.FOR PRESS FIT ON UNGROUND STACK	
C200099676	-	CU40196101 REAR HSG.FOR PRESS FIT ON UNGROUND STACK	
C200099677	-	CU40196101 553013403 WITH LUGS REMOVED	
C200099678	-	CU40196101 553013369 WITH LUGS REMOVED	
C200099679	-	SHAFT-LEAD SCREW REF.340013443 (7.856 TO BE 8.235)	
C200099680	-	COMBINE RETURN PATH C557072175&C506002139)& COIL AS AN ASS'Y	
C200099681	-		
C200099682	-	ROTOR SUB DEI#03011	
C200099683	-	ROTOR DEI#03011	
C200099684	-	STA.&HSG.S/A C550080874 EXCEPT PER DEI#03010	
C200099685	-	ROTOR S/A C551073250 EXCEPT PER DEI#03010	
C200099686	-	SHAFT-SAME AS 340002361 EXCEPT GEAR DATA 1 INSTEAD OF 2	
C200099687	-	PICKOFF CORE-A201A515-101	
C200099688	-	ROTOR STACK-SAME AS 552052706 EX.31 1/2" SKEW	
C200099689	-	IDENT.NO. FOR A314A421-01 HOUSING TADAR	
C200099690	-	STABELIZERS-VENDOR #790-676 "OLD DOMINION"	
C200099691	-	STABELIZERS-VENDOR #790-677 "OLD DOMINION"	
C200099692	-	15-BALL BALL BEARING NHB#S188K13/85 ABEC 5	
C200099693	-	DEI#03013 STATOR STACK-DM	
C200099694	-	DEI#03013 ROTOR-DM	
C200099695	-	DEI#03013 ROTOR SUB-DM	
C200099696	-	DEI#03013 STA.& HSG.-DM	
C200099697	-	HSG-FRONT 553013403 NEW PROCESS	
C200099698	-	HSG-REAR 553013369 NEW PROCESS	
C200099699	-	DEI#03013 ROTOR D.M.	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099700	-	C703925204 MODIFIED TO C703925211	
C200099701	-	553013402 REAR HSG. THAT HAS BEEN STRESS RELIEVED	
C200099702	-	ROTOR C551073428 MODIFIED PER DEI#01301	
C200099703	-	SHAFT C340013500 MODIFIED PER DEI#01301	
C200099704	-	SLEEVE C375022293 MODIFIED PER DEI#01301	
C200099705	-	ROTOR-SALVAGE METHOD	
C200099706	-	HSG-REAR REF.553013369	
C200099707	-	HSG-FRONT REF. 553013403	
C200099708	-	SHAFT-TEST PIECE FOR WELD 340012655	
C200099709	-	LAMINATION-SAME AS C552002329 EXCEPT .0005 TO BE .0008 CM41005018 & 030	
C200099710	-	STACK-SAME AS C200019943 EXCEPT USE LAM C200099709 CM41005018 & 030	
C200099711	-	ROTOR SUB-SAME AS C551052501 EXCEPT USE STACK C200099710 CM41005018 & 030	
C200099712	-	ROTOR SUB-SAME AS C551062231 EXCEPT USE STACK C200099710 CM41005018 & 030	
C200099713	-	ROTOR SUB-SAME AS C551052512 EXCEPT USE STACK C200099710 CM41005018 & 030	
C200099714	-	ROTOR SUB-SAME AS C551052511 EXCEPT USE STACK C200099710 CM41005018 & 030	
C200099715	-	ROTOR SUB-SAME AS C551062296 EXCEPT USE STACK C200099710 CM41005018 & 030	
C200099716	-	ROTOR-SAME AS C551012370 EXCEPT USE SUB C200099711	
C200099717	-	ROTOR-SAME AS C551071349 EXCEPT USE SUB C200099712	
C200099718	-	ROTOR-SAME AS C551071388 EXCEPT USE SUB C200099713	
C200099719	-	ROTOR-SAME AS C551071941 EXCEPT USE SUB C200099715	
C200099720	-	ROTOR-SAME AS C551012301 EXCEPT USE SUB C200099713	
C200099721	-	ROTOR-SAME AS C551012387 EXCEPT USE SUB C200099711	
C200099722	-	ROTOR-SAME AS C551071929 EXCEPT USE SUB C200099714	
C200099723	-	SLEEVE-REF. C375022195	
C200099724	-	COMP.BOARD ASS'Y FOR C703181008	
C200099725	-	552052025 WITH WHIRLCLAD	
C200099726	-	WIRE HARNESS FOR 11732905 HUGHES SUB-ASS'Y	
C200099727	-	WIRE HARNESS FOR 11732905 HUGHES SUB-ASS'Y	
C200099728	-	DETERGENT-TRITON X 100 SOURCE:RHOM & HAAS,PHILADELPHIA ,PA	
C200099729	-	ACTIVATED CARBON CHARCOAL 6-14 MESH FISHER SCIENTIFIC CAT.#05-685-A	
C200099730	-	553013369 WITH WHIRLCLAD CLEARANCE	
C200099731	-	553013403 WITH WHIRLCLAD CLEARANCE	
C200099732	-	MARKEM STAMP FOR CU09600024	
C200099733	-	OBSOLETE-EHO 2-10-82 (HAINES LAM)	
C200099734	-	OBSOLETE-EHO 2-10-82 (HAINES LAM)	
C200099735	-	SHAFT-SAME AS C340012982 EXCEPT EXTENSION=2.250 X .2499	
C200099736	-	C557011027 MAGNET COATED ON SIDES WITH C101061128,.005 +.001 -.001 THICK	
C200099737	-	SAME AS C551052358 EXCEPT USING C200089967 STACK	
C200099738	-	SAME AS C551072488 EXCEPT NULL READS BETWEEN 30MV & 60MV	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099739	-	DISC FOR C200083084 CAN'T ANGLE SENSOR	
C200099740	-	HUB FOR C200083084 CAN'T ANGLE SENSOR	
C200099741	-	375022255 ROTOR SLEEVE BUT KEYSTONE Z29 POWDER	
C200099742	-	SAME AS C200062656 EXCEPT SHORT LEADS	
C200099743	-	SAME AS C200062904 EXCEPT SHORT LEADS	
C200099744	-	SAME AS C552052706 EXCEPT SKEW ANGLE OF 30.25 DEGREE +.75 DEGREE - .75 DEGREE	
C200099745	-	SAME AS 551073549 ROTOR EXCEPT KEYSTONE Z29 SLEEVES	
C200099746	-	SAME AS C554002933 EXCEPT	
C200099747	-	SAME AS C553013286 HSG. OPER 4 PROCESS	
C200099748	-	SAME AS C554002913 ENDBELL OPER 04	
C200099749	-	SAME AS C553014256 HSG.OPER 04	
C200099750	-	SAME AS C552002480 EXCEPT (.014 THK)	
C200099751	-	ROTOR ASS'Y(SAME AS C551073457 EXCEPT USE MAG.WIRE BELOW)	
C200099752	-	ESTEROL 180,#38 AWG MAG.WIRE(USE IN C200099751 ROTOR ASS'Y)	
C200099753	-	RYTON-R4 THERMOPLASTIC	
C200099754	-	SAME AS 551062183 EXCEPT W/O INSULATION	
C200099754A	-	SAME AS 551062183 EXCEPT USING 200099744 STACK	
C200099755	-	SAME AS C552052910 EXCEPT W/ASHEVILLE INSULATED LAM	
C200099756	-	SAME AS C552052910 W/UNINSULATED LAMS	
C200099757	-	SAME AS C550080863 EXCEPT W/C200099755 STACKS	
C200099758	-	SAME AS C550080863 EXCEPT W/C200099756 STACKS	
C200099759	-	SAME AS 375022401 EXCEPT EXTRUDED STOCK (SHUGART)	
C200099760	-	SAME AS C551071869 EXCEPT USE 200099754 ROTOR SUB	
C200099761	-	ROTOR SLEEVE FOR .9DEGREE STEPPER-WITH SPECIAL I.D	
C200099762	-	ROTOR FOR .9 DEGREE STEPPER-WITH C200099761 SLEEVE	
C200099763	-	COVER DET.1 83-82-12832	
C200099764	-	SLEEVE DET.2 83-82-12832	
C200099765	-	SLEEVE & SHAFT ASS'Y (CU09628030)	
C200099766	-	SAME AS C552052993 EXCEPT SKEW ANGLE OF 27 DEGREE +/-0.5 DEGREES	
C200099767	-	SAME AS C552052993 EXCEPT SKEW ANGLE OF 24 DEGREE +/-0.5DEGREES	
C200099768	-	SAME AS C551062189 EXCEPT USE 200099766 STACK	
C200099769	-	SAME AS C551062189 EXCEPT USE 200099767 STACK	
C200099770	-	SAME AS C340013576 EXCEPT WITH U'CUT	
C200099771	-	SAME AS A202A267-01 P.O & COIL EXCEPT BOBBIN HAS 395 TURNS INSTEAD OF 375	
C200099772	-	SAME AS C375022401 EXCEPT .510 DIA IS .505	
C200099773	-	SAME AS 552052910 (DEI#01302)	
C200099774	-	SAME AS 550080863 (DEI#01302)	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099775	-	SAME AS 552052911 (DEI#01302)	
C200099776	-	SAME AS 200086278 (DEI#01302)	
C200099777	-	SAME AS 553013455 (MADE FROM BAR STOCK IN HOUSE) GSK	
C200099778	-	SAME AS 654002965 (MADE FROM BAR STOCK IN HOUSE) GSK	
C200099779	-	SAME AS 553013455 (MADE IN HOUSE FROM BLANK)	
C200099780	-	SAME AS 554002965 (MADE IN HOUSE FROM BLANK)	
C200099781	-	HOUSING 1836	
C200099782	-	BRG.BUSHING 1836	
C200099783	-	FR.HSG.BLK.	
C200099784	-	FR.HSG.MACH.	
C200099785	-	REAR HSG.BLK.	
C200099786	-	REAR HSG.MACH.	
C200099787	-	RING FOR MATAMOROS FOR REPAIR OF PILOT DIA.	
C200099788	-	SAME AS C551002032 EXCEPT USE 200099737 ROTOR SUB	
C200099789	-	FR.HSG MACH.WITH .6249 +.0003 -.0000 DIA THRU	
C200099790	-	REAR HSG.MACH.WITH .8749 +.0003 -.0000 DIA THRU	
C200099791	-	SAME AS 553013252 EXC.416 STAINLESS REF DEI#01302	
C200099792	-	SAME AS 307002300 EXC.416 STAINLESS REF DEI#01302	
C200099793	-	SAME AS 552002569 EXC 4750 ATL REF DEI#01302	
C200099794	-	SAME AS 5520025698 EXC 4750 ATL REF DEI#01302	
C200099795	-	HERMASEAL	
C200099796	-	REAR HSG 1836 SAME AS 553013369-KUMMER PROCESS	
C200099797	-	FT HSG.1836 SAME AS 553013403-KUMMER PROCESS	
C200099798	-	ROTOR SAME AS C551012346 EXCEPT STACK O.D. MACHINED (CANNOT USE IN 10145)	
C200099799	-	ROTOR SUB SAME AS 551062165 EXCEPT SHAFTS IS 340010651	
C200099800	-	553013402 WITH .625 BORE	
C200099801	-	SAME AS 552052911 W/.039 +/- .002 CHRD DEI 03016	
C200099802	-	SAME AS 551075059 EXC.SEE DEI 03016	
C200099803	-	CT40195012 STATORS BUT WITH 459 TURNS	
C200099804	-	10000 396 BRASS CUT INTO 1/2 LENGTH FOR PLATE ROOM	
C200099805	-	C340013576 SHAFT	
C200099806	-	C200088946 RTR&HUB ASY(REF)LESS C200088941 GUIDE-WIRE (SPACER SLEEVE) C551073583 ROTOR B&C308022330	
C200099807	-	REAR HOUSING-NO EARS-.8749 BRG BORE 553013369	
C200099808	-	FR.HSG.-NO EARS-REF.553013403	
C200099809	-	SAME AS C552052511 (DEI 03018)	
C200099810	-	SAME AS C200086278 (DEI 03018)	
C200099811	-	SAME AS C552052910 (DEI 03018)	
C200099812	-	SAME AS C550080863 (DEI 03018)	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099813	-	FORM-COIL SAME AS C506012176 (DIFF.WHIRLCLAD)(GREEN)ENG.EVAL.	
C200099814	-	GEAR SHAFT FOR C310132164 GEAR & SHAFT ASS'Y	
C200099815	-	GEAR SHAFT FOR C310132167 GEAR & SHAFT ASS'Y	
C200099816	-	GEAR SHAFT FOR C310132163 GEAR & SHAFT ASS'Y	
C200099817	-	GEAR SHAFT FOR C310132161 GEAR 7 SHAFT ASS'Y	
C200099818	-	GEAR HEAD ASSY (FOR ROLL ACTUATOR ASSY CU09609056)	
C200099819	-	GEAR SHAFT FOR C310132168 GEAR & SHAFT ASS'Y	
C200099820	-	GEAR SHAFT FOR C310132160 GEAR & SHAFT ASS'Y	
C200099821	-	GEAR HEAD ASSY (FOR PITCH ACTUATOR ASSY CU09609055)	
C200099822	-	GEAR SHAFT FOR C310132166 GEAR & SHAFT ASS'Y	
C200099823	-	GEAR SHAFT FOR C310132162 GEAR & SHAFT ASS'Y	
C200099824	-	GEAR SHAFT FOR C310132165 GEAR & SHAFT ASS'Y	
C200099825	-	LACING TAPE (MIL-T-43435 TYPE 1,FINISH B,SIZE 5)	
C200099826	-	CONNECTOR (AMPHENOL #M81511-01ED01P1)	
C200099827	-	PLUG SEAL (AMPHENOL#M81511-15-22)	
C200099828	-	GEAR SHAFT FOR C310132149 GEAR & SHAFT ASSY	
C200099829	-	GEAR SHAFT FOR C310132150 GEAR & SHAFT ASS'Y	
C200099830	-	BRASS SPACER FOR 111135 SEAL ASSY	
C200099831	-	GEARHEAD AND SYHCHRO ASSY	
C200099832	-	200099807 REAR HSG.WITH COIL CLEARANCE	
C200099833	-	200099808 FRONT HSG.WITH COIL CLEARANCE	
C200099834	B	TEST PANEL SUPPLIER IS Q-LAB CORPORATION, SUPPLIER P/N IS SP-110207	77396
C200099835	-	SAME AS C375022165 EXCEPT SPECAIL MATERIAL	
C200099836	-	GEAR TRAIN ASSY (TILT ACTUATOR ASSY)	
C200099837	-	320002750 SCREW SHORTENED BY .030"	
C200099838	-	320002751 SCREW SHORTENED BY .030"	
C200099839	-	PLATE FOR 200088537&538 GEARHEAD	
C200099840	-	MAG.WIRE S/A C200052068 EXCEPT PURCHASE OR SELECT RES.4.998-5.250 FOR 10 FT.AT 25 DEGREE C	
C200099841	-	552053099 STACK NOT INDEXED	
C200099842	-	340013619 SHAFT SPEC.SOA 746	
C200099843	-	GEAR SHAFT FOR C310130116 GEAR & SHAFT ASSY	
C200099844	-	STAKING WASHER FOR C310130116 GEAR & SHAFT ASSY	
C200099845	-	HUB FOR C310110337 GEAR & HUB ASSY	
C200099846	-	STAKING WASHER FOR C310110337 GEAR & HUB ASS'Y	
C200099847	-	DETAIL"E"GEAR BLANK FOR C310110337 GEAR & HUB ASS'Y	
C200099848	-	DETAIL"F"GEAR BLANK FOR C310110337 GEAR & HUB ASS'Y	
C200099849	-	RETAINER (WINDING & INSULATOR) SIMILAR TO C343002517	
C200099850	-	SAME AS C551071340 EXCEPT OD TO BE .4065-.4070 & WDG AS 551072541	
C200099851	-	SAME AS 557A079-101 R.PATH,EXCEPT MADE FROM 416 S.S.	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099852	-	SAME AS A558A059-01 EXCEPT USE C200099851 RET.PATH(416 S.S. MAT'L)	
C200099853	-	INSERT FOR C200042280 INSERT & COVER ASSY	
C200099854	-	BUSHING FOR COMPOSITE CLUTCH (BRASS)	
C200099855	-	SAME AS C550081137 (DEI 03019)	
C200099856	-	SAME AS C553013533 (DEI 03019)	
C200099857	-	SAME AS C552002750 (DEI 03019)	
C200099858	-	SAME AS C552053111 (DEI 03019)	
C200099859	-	SAME AS C375022432 (DEI 03019)	
C200099860	-	SAME AS C554002998 (DEI 03019)	
C200099861	-	SAME AS C305002304 (DEI 03019)	
C200099862	-	BEARING & PIN PACKAGE FOR RELIANCE GEAR,TEXAS INST GEARHEAD	
C200099863	-	TERM.STUD C200109131 LENGTH ALTERED FOR C200088930 ASS'Y	
C200099864	-	SELECTED FROM JANTX2N3879 FOR 1140 CARD USE ONLY	
C200099865	-	SELECTED FROM C200083927	
C200099866	-	SELECTED FROM JANTX2N3879 FOR 1133,1135 & 1139 CARD	
C200099867	-	SAME AS C490164052 EXCEPT 1.5-2.0 MG OF LUBE	
C200099868	B	JSTD-006 FLUX CORE WIRE SOLDER, ALLOY: Sn63Pb37, DIAMETER: .030" +/- .005, FLUX TYPE: ROLO, FLUX PERCENTAGE BY WEIGHT 2%-3.5%	86777
C200099869	A	SOLDER-PB88BW000000.810.5 REF./PURCH.ALPHA, KESTER	71598
C200099870	-	SOLDER-QQ-S-571SN5WS 0.032 DIA.,REF./PURCH ALPHA, KESTER	
C200099871	B	SN63PB37 IAW J-STD-006, BAR SOLDER	NOC-81359 4/6/2011
C200099872	-	FLUX-MIL-F-14256 TYPE RMA,PURCH ALPHA 611,KESTER 196	
C200099873	A	FLUX-MIL-F-14256,TYPE RMA,FOAMING,PURCH ALPHA 611F OR 615	72134
C200099874	A	THINNER PURCH ONLY ALPHA 438 (USE WITH ALPHA 611F ONLY)	73380
C200099875	-	THINNER PURCH ONLY ALPHA 411 (USE WITH ALPHA 611 OR KESTER 196 ONLY)	
C200099876	-	STA.& HSG.SAME AS C550031134 EXCEPT 876 IS FOR NON CRITICAL UNITS CM01036700,707 & CM41034009	
C200099877	-	C553013492 HOUSING AND C557002371 MAGNET ASS'Y	
C200099878	-	SAME AS C551072613 EX CAST SLEEVE FROM PERM MAG. CORP	
C200099879	P	CLAMP ASSY TAKES PLACE OF C336002170&171 CLAMPS (SEE OPERATION SHEETS)	74346
C200099880	-	552053025 STACK WHIRLCLAD BUT NOT OD GROUND	
C200099881	-	553013510 F.HSG WITH W'CLAD CLEARANCE	
C200099882	-	553013512 R.HSG.WITH W'CLAD CLEARANCE	
C200099883	-	GEARHEAD ASSY FOR CASA 399802	
C200099884	-	GEAR SHAFT FOR C310132185 GEAR & SHAFT ASS'Y	
C200099885	-	GEAR BLANK FOR C310132185 GEAR & SHAFT ASS'Y	
C200099886	-	FLUX: NEY AFC	
C200099887	-	SAME AS 552052100 EXCEPT LAM#9075T4314- 20 SLOTS	
C200099888	-	SAME AS C200019549 EXCEPT LAM IS .014 TH.INSTEAD OF .010	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099889	-	SAME AS 552052277 EXCEPT LAM IS .014 TH.INSTEAD OF .010	
C200099890	-	SAME AS 200019838 EXCEPT LAM IS .014 TH. INSTEAD OF .010	
C200099891	-	SAME AS 552052189 EXCEPT LAM IS .014 TH.INSTEAD OF .010	
C200099892	-	SAME AS C552002281 EXCEPT .014 THK	
C200099893	-	SAME AS 552002282 EXCEPT .014 THK	
C200099894	-	SAME AS 552002178 EXCEPT .014 THK	
C200099895	-	SAME AS 552002177 EXCEPT .014 THK	
C200099896	1	CORE (TORIDAL)	79575
C200099897	-	ALUM FOIL SHIELD	
C200099898	-	SAME AS C552052137 EXCEPT .480 +.010 -.000 TO BE .185 +.005 -.005	
C200099899	-	SAME AS C550042760 EXCEPT 20 SLOT&USES C200099887 STACK	
C200099900	-	SAME AS C550042717 EXCEPT 20 SLOT&USES C200099887 STACK	
C200099901	-	SAME AS D780783-02 EXCEPT OD	
C200099902	-	STA.&HSG.PER DEI#1306 USIG C200099601 HSG.	
C200099903	-	HSG& ENDBELL PER DEI#1306 USING C200099602 E.B. & C200099513 HSG	
C200099904	-	STA.& HSG. PER GEI 1306 USING C200099602 & C200099513 HSG	
C200099905	-	C551072093 LAM.WITH ANNEAL & INSULAZE PER C190000101	
C200099906	-	A315P094 SLEEVE	
C200099907	-	TEST HSG.GYRO A314A423	
C200099908	-	RETAINER (WINDING)SIMILAR TO 343002517 STEPPER MOTOR	
C200099909	-	STACK LIKE 552053072 BUT NO INFORMATION	
C200099910	-	FRONT HOUSING LIKE 553013584 BUT 509 BLANK	
C200099911	-	REAR HOUSING LIKE 553013583 BUT 511 BLANK	
C200099912	-	WINDOW CONTROL SAME AS C703925204 EXCEPT	
C200099913	-	SAME AS 553012260 EXCEPT MOUNTING DIA NOT COMPLETE	
C200099914	-	SAME AS C550081122 5PC ENG EVAL FOR IMPROVED FITS	
C200099915	-	SAME AS C550081122 10PC ENG EVAL FOR CENTERUNE CONST.	
C200099916	-	GEAR HEAD ASSY;FOR PARTS SEE ASSY DWG. CU09609149	
C200099917	-	GEARSHAFT FOR C310132197	
C200099918	-	GEARSHAFT FOR C310132198	
C200099919	-	GEAR BLANK	
C200099920	-	GEAR BLANK	
C200099921	-	GEARSHAFT FOR C310142014	
C200099922	-	GEAR SHAFT FOR C310142015	
C200099923	-	GEAR BLANK FOR C310142014	
C200099924	-	GEAR BLANK FOR C310142015	
C200099925	-	GEAR SHAFT FOR C310082772	
C200099926	-	GEAR SHAFT FOR C310132199	
C200099927	-	GEAR BLANK FOR C310082772	



# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099928	-	GEAR BLANK FOR C310132199	
C200099929	-	ROTOR TEST RINGS	
C200099930	-	WHIRLCLAD STACKS .9 DEGREE STEPPER	
C200099931	-	GEAR HEAD ASSY FOR CU09609055	
C200099932	-	MS51957-16 SCREW W/SLEEVEING	
C200099933	-	MS51957-17 SCREW W/SLEEVEING	
C200099934	-	GEAR HEAD ASSY FOR CU09609056	
C200099935	-	WINDING RETAINER .9 STEPPER	
C200099936	-	GEAR HEAD ASSY FOR CU09609057	
C200099937	-	NUMBER OPEN	
C200099938	-	NUMBER OPEN	
C200099939	-	GEAR HEAD ASSY FOR CU09609058	
C200099940	-	STATORS WIND/INSERT CU40196901	
C200099941	-	SCREW W/SLEEVEING (MS51957-16)	
C200099942	-	SCREW W/SLEEVEING (MS51957-17)	
C200099943	-	STACK FOR C551063031,C552002773 LAM 64 APPROX	
C200099944	-	986617-00 CORES HEAT UNIT TO 2150 DEGREES F MADE INTO ROTORS	
C200099945	-	SAME AS 550052385 EXCEPT USE HY-MU#80 LAMINATIONS SOA 315	
C200099946	-	SAME AS 550052385 EXCEPT LAMS ARE COATED PER EMI#50160	
C200099947	-	INSULATION FOR 12281135	
C200099948	-	SAME AS STA.HSG.C550031561 EXCEPT USE HSG.C200099949	
C200099949	-	SAME AS HSG C553012756 EXCEPT LECTRO ETCH MEXICO	
C200099950	-	SAME AS C490314057 EXCEPT 20/25% FILL OF ASHEVILLE 22	
C200099951	-	SAME AS C490264057 EXCEPT 20/25% FILL OF ASHEVILLE 22	
C200099952	-	HSG.BLANKS 553013509&511 REF	
C200099953	-	PIN-SAME AS C200109504 EXCEPT .455 +000 -005 LONG	
C200099954	-	ROTOR SAME AS C551073431 EXCEPT PER I.D.O.#80-82-16728	
C200099955	-	D636540-05 ROTOR BUT USE 200099956 CORE	
C200099956	-	200059308 ROTOR CORE WITH .125 END RINGS	
C200099957	-	(FINISH BORE)C554002591 END BELL FOR CENTER LINE ASS'Y	
C200099958	-	(FINISH BORE & MTG DIA'S) C553002077 HSG.FOR CENTER LINE ASSY	
C200099959	-	BEARING BUSHING SIMILAR TO 986252-00	
C200099960	-	STATOR 717761-03 WITH 200099959 BUSHINGS	
C200099961	-	HOUSING REF.C553013434	
C200099962	-	BRUSH HOLDER SAME AS C558042811 EXCEPT "+"&"-" ARE REVERSED	
C200099963	-	GEAR HEAD	
C200099964	-	COMBINE C557072175 RET.PATH & C506002520 COIL & MAKE AS AN ASY	
C200099965	-	GEAR SHAFT FOR C310132193 GEAR & SHAFT ASSY	
C200099966	-	GEAR HUB FOR C310132193 GEAR & SHAFT ASS'Y	

# PRODUCT LOG

(See Operation Sheets if Available)

NUMBER	Rev.	DESCRIPTION	NOC*
C200099967	-	GEAR SHAFT FOR C310132194 GEAR & SHAFT ASS'Y	
C200099968	-	GEAR HUB FOR C310132194 GEAR & SHAFT ASS'Y	
C200099969	-	EXPERMENTAL SLEEVE FOR CT09600001 D.C.MTR	
C200099970	-	STATOR&SUPPORT SAME AS C550052385 EXCEPT LAM STOCK MADE OF C552002200 SOA814 SOA 816	
C200099971	-	LAM ASS'Y FOR C551062647 ROT SUB	
C200099972	-	SAME AS C552052325 EXCEPT LAM #552002339-SOA 152	
C200099973	-	SAME AS C554002843 EXCEPT INCLUDES RET.PATH	
C200099974	-	SAME AS 556002238 SOA#154	
C200099975	-	ROTOR FOR CU40196902	
C200099976	-	REAR HSG FOR CU40196902	
C200099977	-	EXPERIMENTAL PART (END BELL)	
C200099978	-	EXPERIMENTAL ROTOR SLEEVE	
C200099979	-	S/A C552052812 EXCEPT HEIGHT TO BE 1.498 +.014 -.000 ON SOA	
C200099980	-	ROTOR SUB FOR HARPOON TACH-USING TANG COMM	
C200099981	-	ROTOR FOR HARPOON TACH-USING TANG COMM	
C200099982	-	ROTOR SHAFT FOR DIE CAST ROTOR & TANG COMM	
C200099983	-	ROTOR SUB FOR DIE CAST ROTOR & TANG COMM	
C200099984	-	ROTOR FOR DIE CAST ROTOR & TANG COMM	
C200099985	-	WINSORLUBE L245X FOR 200086676	
C200099986	-	MOLDED HEATSINK INSULATOR (12281138)	
C200099987	-	ALUM SLEEVE FOR C200109790 ASS'Y	
C200099988	-	SAME AS 552052911 EXCEPT SKEW TO BE .034 +.002 -.002 DEI01308	
C200099989	-	SAME AS 552052911 EXCEPT SKEWE TO BE .039 +.002 -.002 DEI 01308	
C200099990	-	SAME AS 552052911 EXCEPT SKEW TO BE .044 +.002 -.002 DEI01308	
C200099991	-	SAME AS 552092911 EXCEPT SKEW TO BE .049 +.002 -.002 DEI01308	
C200099992	-	SME AS 200086278 EXCEPT (WINDING & SKEW) .034 +.002 -.002 DEI01308	
C200099993	-	SAME AS 200086278 EXCEPT WINDING & SKEW .039 +.002 -.002 DEI01308	
C200099994	-	SAME AS 200086278 EXCEPT WINDING & SKEW .044 +.002 -.002 DEI01308	
C200099995	-	SAME AS 200086278 EXCEPT WINDING & SKEW .049 +.002 -.002 DEI01308	
C200099996	-	MATCHED SET C200088452 CAPACITORS	
C200099997	-	ELECTROFILM LUBE LOCK 5306 SAME AS C180000833	
C200099998	-	9 DEGREE STEPPER ROTOR 30A CRUMAX MAG AND SPACER	
C200099999	-	9 DEGREE STEPPER ROTOR 2 EA. 30A CRUMAX MAG AND SPACER	